




## Burr Z7 – medium, diamond cut, Carbide, Type: E1220



### Order data

Order number	540750 E1220
GTIN	4045197967213
Item class	52D

### Description

#### Version:

Shank Ø 6 mm.

**HOLEX** burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Shape description	teardrop
Toothing grit designation	medium
Shank Ø	6 mm
Head Ø	12 mm
Type of cut	staggered teeth
Overall length	60 mm
Shape	E1220
Tooth type abbreviation	Z7

Head length	20 mm
Series	#Tooth configuration Z7
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	$V_c$	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		