

Garant
Cutting disc, high-performance version EXTRA THIN, steel, Disc Ø: 230mm


Order data

Order number	563262 230
GTIN	4045197967534
Item class	51M

Description

Version:

New **high-performance version** using state of the art technology with significant productivity advantages and excellent cutting qualities. **Increased cutting performance** due to rough free-grinding side faces; **improved service life**.

The thinness of the disc allows **very quick** cutting **with low force and optimum time saving**.

Clean cut edges, virtually no burrs.

Special type for **steel**, high performance version.

Specification:

A46S-BF.

Technical description

Disc thickness	1.9 mm
Shape	41
Shape description	flat
maximum speed	6600 min ⁻¹

Disc Ø	230 mm
Bore Ø	22.23 mm
Specification	A46S-BF
for material thicknesses	5.7 mm
Grinding medium code	A
recommended approach angle	90 degrees
optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		