

Dräger**Measuring tubes, set of 10 pieces, Type: CO****Order data**

Order number	097202 CO
GTIN	4026056014804
Item class	09J

Description**Version:**

Each measuring tube consists of a thin glass tube melted at the ends to seal it. Inside there is a chemically reactive filling layer. To perform a measurement, break the ends off the tube and insert it into the gas detection pump. The pump compresses the air that is to be tested, which causes the filling layer to change colour when it reacts with the respective gas. The concentration can be read off on an integral scale.

Dräger tubes for measuring carbon monoxide, ammonia gas, hydrogen sulphide and formaldehyde.

Note:

For safety technical reasons gas detection devices cannot be returned.

A selection of around 300 different types of tube is available on request. These allow more than 500 substances to be measured quickly and easily, in many different concentrations.

Sensor for gas type: Carbon monoxide

Measuring time 1: 2.5 min

Standard measuring range 1: 5 - 150 ppm

Measuring time 2: 30 s

Standard measuring range 2: 100 - 700 ppm

Technical description

Sensor for gas type	Carbon monoxide
Standard measuring range 1	5 - 150 ppm
Measuring time 1	2.5 min
Standard measuring range 2	100 - 700 ppm
Measuring time 2	30 s
Type of product	Single gas detection device