



Cutting disc SGP STEEL EXTRA THIN, Disc Ø: 125mm



Order data

Order number	563440 125
GTIN	4007220103920
Item class	55T

Description

Version:

Extra thin **high performance cutting disc** for very quick low-burr cutting with low thermal stress and easy ergonomic cut guidance. Very tough, very high cutting performance and outstanding service life.

Specification:

A60Q-CERAMIC SGP STEEL.

Technical description

Shape description	flat
Disc thickness	1 mm
Disc Ø	125 mm
Bore Ø	22.23 mm
for material thicknesses	3 - 5 mm
Grinding medium code	Ceramic
recommended approach angle	90 degrees

optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable only under restricted conditions		
dry	suitable		