

Garant

Solid carbide barrel milling cutter, conical form $\alpha/2=27^\circ$ PPC, DLC, \varnothing f8 DC / R2: 16/1000mm

**Order data**

Order number	207533 16/1000
GTIN	4045197989086
Item class	11X

Description**Version:**

High-performance tool for **exceptionally efficient finish machining of free-form surfaces**. For outstanding surface qualities in a **very short machining time**. For use on modern 5-axis milling machines with CAD / CAM support.

The end face geometry is designed so that the chips, especially those formed by the end radius, are of optimum shape and have optimum evacuation characteristics. For this purpose the number of cutting edges is reduced to the number of effective end face cutting edges.

Recommendation:

We recommend 0.05 to 0.2mm as an allowance for finishing operations.

Note:

R_2 represents the effective radius on the tool.

Cannot be reground!

For machining walls and overcoming obstructions.

Technical description

No. of teeth Z	4
Corner radius R_1	3 mm
Shank $\varnothing D_s$	16 mm
Overall length L	90 mm
Helix angle	30 degrees
Cutting edge $\varnothing D_c$	16 mm
Feed f_z for copy milling in short-chipping aluminium	0.11 mm

Flute length L_c	12.5 mm
Feed f_z for side milling in short-chipping aluminium	0.09 mm
Effective radius R_2	1000 mm
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal \varnothing	f8
Direction of infeed	horizontal
Cutting width a_e for milling operation	0.05×D for side milling
Cutting width a_e for milling operation	0.05×D for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	PPC
Colour ring	yellow
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	330 m/min	N
Aluminium (short chipping)	suitable	300 m/min	N
Alu > 10% Si	suitable	230 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

Services

Shank grinding Type HB

129100 HB