

Garant

Solid carbide barrel milling cutter, conical form $\alpha/2=18^\circ$ PPC, DLC, \varnothing f8 DC / R2: 6/250mm


Order data

Order number	207531 6/250
GTIN	4045197989055
Item class	11X

Description
Version:

High-performance tool for **exceptionally efficient finish machining of free-form surfaces**. For outstanding surface qualities in a **very short machining time**. For use on modern 5-axis milling machines with CAD / CAM support.

The end face geometry is designed so that the chips, especially those formed by the end radius, are of optimum shape and have optimum evacuation characteristics. For this purpose the number of cutting edges is reduced to the number of effective end face cutting edges.

Recommendation:

We recommend 0.05 to 0.2mm as an allowance for finishing operations.

Note:

For machining walls and overcoming obstructions.

R_2 represents the effective radius on the tool.

Cannot be reground!

Technical description

Helix angle	30 degrees
Flute length L_c	8 mm
Effective radius R_2	250 mm
Cutting edge $\varnothing D_c$	6 mm
Feed f_z for side milling in short-chipping aluminium	0.04 mm
Overall length L	60 mm
Feed f_z for copy milling in short-chipping aluminium	0.05 mm

Corner radius R_1	0.5 mm
Shank $\varnothing D_s$	6 mm
No. of teeth Z	4
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal \varnothing	f8
Direction of infeed	horizontal
Cutting width a_e for milling operation	0.05×D for side milling
Cutting width a_e for milling operation	0.05×D for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	PPC
Colour ring	yellow
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	330 m/min	N
Aluminium (short chipping)	suitable	300 m/min	N
Alu > 10% Si	suitable	230 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

Services

Shank grinding Type HB

129100 HB