

Garant
GARANT Master Titan solid carbide end torus cutter HPC, TiAlN, Ø h9 DC: 8mm

Order data

Order number	206288 8
GTIN	4045197989529
Item class	11Z

Description
Version:

Tolerance: Corner radius $R_1 = \pm 0.01$ mm.

Special centre cutting edge geometry for traverse milling at very high feed rates.

Application:

For copy and traverse milling of titanium under HPC conditions.

Using special milling strategies **very high rates of metal removal can be achieved.**

Note:

Regrinding not recommended.

Technical description

Overhang length L_1 incl. recess	40 mm
Overall length L	100 mm
Shank $\varnothing D_s$	8 mm
No. of teeth Z	5
Cutting edge $\varnothing D_c$	8 mm
Recess $\varnothing D_1$	7 mm
Flute length L_c	4.8 mm
Dimension $a_{p\max}$ transverse	0.5 mm
Programming radius	1.5 mm
Setting angle κ	15 degrees

Feed f in titanium > 850 N/mm ²	0.1 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal Ø	h9
Helix angle	15 degrees
Direction of infeed	horizontal, oblique and vertical
Cutting width a _e for milling operation	Full slot cutting depth 1×D
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	pink
Type of product	End torus mill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable	80 m/min	S
wet maximum	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------