


Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 5,5mm

Order data

Order number	GG1293 5,5
GTIN	4045197990815
Item class	GGN

Description
Version:

Dimensions similar to **DIN 6527**. Improved coating for general-purpose applications in steel and cast iron.

Same as No. 202293.

Technical description

Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Feed f_z for slot milling in steel < 750 N/mm ²	0.03 mm
Tolerance nominal Ø	e8
No. of teeth Z	3
Shank Ø D_s	6 mm
Overhang length L_1 incl. recess	21 mm
Helix angle	45 degrees
Corner chamfer width at 45°	0.1 mm

Shank form	HB
Overall length L	57 mm
Cutting edge $\varnothing D_c$	5.5 mm
Recess $\varnothing D_1$	5.3 mm
Feed f_z for side milling in steel $< 750 \text{ N/mm}^2$	0.04 mm
Flute length L_c	13 mm
Corner chamfer angle	45 degrees
Contents	5
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions	200 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	120 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	110 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	100 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	70 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable only under restricted conditions	60 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	70 m/min	M

INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable only under restricted conditions		
Air	suitable		

Accessories

Solid carbide milling cutter Ø e8 DC 5,5 mm

202293 5,5