

**Garant**
**Stub drill HSS-E-PM HPC, TiAlN, Ø DC h8: 5mm**

**Order data**

Order number	113280 5
GTIN	4045197007537
Item class	11B

**Description**
**Version:**

Tool made of sintered **powder metallurgy HSS** for heavy duty applications. Ground flutes with high concentricity. Generous flute profile.

With point geometry shape A/C from size 2.2 mm.

**Advantage:**

Can be used at increased cutting data.

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Technical description**

Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.04 mm/rev.
Flute length L <sub>c</sub>	26 mm
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	5 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	5 mm
Overall length L	62 mm
Standard	DIN 1897
recommended maximum drilling depth L <sub>2</sub>	18.5 mm
Point angle	130 degrees

Shank	Plain shank
Coating	TiAlN
Tool material	HSS E PM
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	70 m/min	N
Alu > 10% Si	suitable only under restricted conditions	60 m/min	N
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	14 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	20 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	15 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	12 m/min	S
GG(G)	suitable	50 m/min	K
CuZn	suitable only under restricted conditions	60 m/min	N
Oil	suitable		
wet maximum	suitable		

