




Work platform individual module, Type: F



Order data

Order number	966150 F
GTIN	4003866402656
Item class	96Z

Description

Version:

Extremely robust, torsion-resistant, corrosion-proof, and weatherproof aluminium alloy structure. Steps of serrated aluminium plate 555×250 mm.

Modular structure allows changes and extensions.

Add-on modules available for 4 different heights.

The two-step basic module with up to 3 add-on steps is suitable for mobile use. Add-on modules available from module type B.

Standard:

DIN EN 14183.

Technical description

Type of step	Step
Standard	DIN EN 14183
Weight of individual module	5.5 kg
Weight of module combination	19.5 kg
Working height	2.99 m
Platform depth	1.3 m

Rung/step depth	250 mm
Rung/step width	555 mm
Module combination	B+D+E+F
Material	Overall light alloy design; steps of ribbed aluminium plate.
Platform height without railing	0.99 m
Accessibility	single-sided
Number of steps including platform	5
Ladders and platforms load capacity	150 kg
Type of product	Work platform