



## Rung stepladder, all plastic, double-sided access, Number of rungs: 2X10



### Order data

Order number	966060 2X10
GTIN	4003866412587
Item class	96Z

### Description

#### Version:

Rungs and stiles (30×30 mm) made from glass-fibre reinforced plastic for particularly high chemical resistance. High-strength perlon belts prevent splay. Replaceable plastic end caps to prevent slipping.

#### Application:

Safety ladders for special applications in the chemical and pharmaceutical industries, power-stations, gasworks, and waterworks.

#### Standard:

DIN EN 61478 bzw. VDE 0682 Abschnitt 6.5 Kategorie 1/30 KV Hochspannungsprüfung für Leitern aus isoliertem Material ist erfüllt.

**VDE-geprüft** für Arbeiten unter Spannung (1000 V AC, 1500 V DC).

Nach DIN EN ISO 4892-2 Alterungsbeständigkeit 10 Jahre.

### Technical description

Ladder length	3 m
outer width at bottom	0.65 m

Number of steps	2×10
Type of step	Rung
Rung/step depth	30 mm
Standard	DIN EN 61478
high chemical resistance	yes
Material	Rungs and stiles made of glass-fibre-reinforced plastic
Weight	17 kg
Belt to prevent splay	by high-strength Perlon belts
Working height approx.	4.15 m
Accessibility	double-sided
Ladders and platforms load capacity	150 kg
Type of product	Stepladder