

Garant
GARANT Master Titan solid carbide milling cutter HPC, TiAlN, Ø DC: 4mm

Order data

Order number	203029 4
GTIN	4045197991744
Item class	11Z

Description
Version:

Specially ground with **corner radii similar to torus cutters.**

Application:

For milling **titanium and titanium alloys**, with very smooth cutting action for optimum tool life and top metal removal rate.

Technical description

Shank Ø D _s	6 mm
No. of teeth Z	4
Feed f _z for side milling in titanium > 850 N/mm ²	0.018 mm
Shank	DIN 6535 HA to h6
Recess Ø D ₁	3.8 mm
Tolerance nominal Ø	e8
Feed f _z for slot milling in titanium > 850 N/mm ²	0.015 mm
Flute length L _c	11 mm
Overhang length L ₁ incl. recess	16 mm
Overall length L	57 mm
Helix angle	40 degrees
Cutting edge Ø D _c	4 mm

Direction of infeed	horizontal, oblique and vertical
Corner rounding r_v	0.1 mm
Series	Master Titan
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Ti > 850 N/mm ²	suitable	60 m/min	S
wet maximum	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------