

Garant**Bench vice, Jaw width: 150mm****Order data**

Order number	967000 150
GTIN	4045197694102
Item class	91J

Description**Version:****High clamping accuracy due to Vee form precision guide.**

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

Supplied with:

Fasteners for attachment to the workbench.

Colour:

Silver-grey.

Technical description

Jaw capacity	255 mm
Opening direction	opens to the rear
Material	high-strength cast iron (GG 25)
Weight	52 kg
Jaw width	150 mm

Type of product

Machinist's vice

Accessories

Pair of spare jaws smooth ground Jaw width 150 mm	967045 150
Swivel base separate Jaw width 150 mm	967020 150
Bench vice mounting plate	967330
Pair of spare jaws serrated Jaw width 150 mm	967040 150
Bench vice mounting plate, bamboo Size 300X250	967328 300X250