

Garant**Bench vice, Jaw width: 80mm****Order data**

Order number	967000 80
GTIN	4045197693877
Item class	91J

Description**Version:****High clamping accuracy due to Vee form precision guide.**

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

Supplied with:

Fasteners for attachment to the workbench.

Colour:

Silver-grey.

Technical description

Opening direction	opens to the rear
Jaw capacity	100 mm
Weight	6.5 kg
Material	high-strength cast iron (GG 25)
Jaw width	80 mm

Type of product

Machinist's vice

Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of spare jaws smooth ground Jaw width 80 mm	967045 80
Swivel base separate Jaw width 80 mm	967020 80
Pair of spare jaws serrated Jaw width 80 mm	967040 80
Bench vice mounting plate	967330