




Flatness measuring system ProLevel 100, Type: 100



Order data

Order number	467576 100
GTIN	2050002078178
Item class	40N

Description

Version:

Quick, flexible and simple flatness measurement on rectangular, round or complex surfaces.

Advantage:

- **Quick and easy flatness measurement.**
- **Quick generation and saving of templates.**
- **Detector with 70 mm sensor face and 10 µm resolution. Measurements even under poor lighting conditions.**
- **Range 80 m.**
- **Direct evaluation of flatness in 3D and colour. Measurement errors can be detected and corrected directly.**

Supplied with:

Self-levelling T430 rotation laser, R310 laser receiver, RC310 remote control, switchable magnet with Vee base, M8 measurement adaptor, power supply unit, sturdy transport case.

Technical description

Range	80 m
Accuracy (receiver)	$\pm 0.02 + 0.03\%$ linearity mm
Levelling accuracy	± 0.02 mRad
Resolution (receiver)	0.01 mm
Interface	RS 485 & IR
Laser class	2
Type of product	Laser levelling device

