

Garant
Bench vice, Jaw width: 100 mm

Order data

Order number	967000 100
GTIN	4045197693884
Item class	91J

Description
Version:
High clamping accuracy due to Vee form precision guide.

Slides to the rear on opening. High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

Supplied with:

Fasteners for attachment to the workbench.

Colour:

Silver-grey.

Jaw capacity: 145 mm

Weight: 17 kg

Technical description

Material	high-strength cast iron (GG 25)
Opening direction	opens to the rear
Weight	17 kg
Jaw capacity	145 mm

Jaw width	100 mm
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Pair of spare jaws serrated Jaw width 100 mm	967040 100
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of spare jaws smooth ground Jaw width 100 mm	967045 100
Swivel base separate Jaw width 100 mm	967020 100
Height adjuster for vice No. 967000 suitable for vice size 100	967500 100
Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100