

**Garant****Bench vice, Jaw width: 100mm****Order data**

Order number	967000 100
GTIN	4045197693884
Item class	91J

**Description****Version:****High clamping accuracy due to Vee form precision guide.**

**Slides to the rear on opening.** High-strength casting (GG 25) with a pearlitic structure. Long and particularly accurate **Vee form precision guide**. Precise spindle bearing, lead spindle is fully enclosed with trapezoidal thread and hence protected from dirt. Large flat milled anvil area for light shaping work. The hardened steel jaws are grooved and can be exchanged for ground jaws (see spare jaws).

**Supplied with:**

Fasteners for attachment to the workbench.

**Colour:**

Silver-grey.

**Technical description**

Material	high-strength cast iron (GG 25)
Opening direction	opens to the rear
Weight	17 kg
Jaw capacity	145 mm
Jaw width	100 mm

Type of product	Machinist's vice
-----------------	------------------

## Accessories

Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
--	------------

Pair of spare jaws serrated Jaw width 100 mm	967040 100
--	------------

Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
---	------------

Bench vice mounting plate	967330
---------------------------	--------

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
--	----------------

Pair of spare jaws smooth ground Jaw width 100 mm	967045 100
---	------------

Swivel base separate Jaw width 100 mm	967020 100
---------------------------------------	------------

Height adjuster for vice No. 967000 suitable for vice size 100	967500 100
---	------------

Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
---	------------

Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
---	------------

Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
---	------------

Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
--	------------

Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
--	------------

Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
---	------------

Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
--	------------