


Jobber drill HSS-E N, uncoated, Ø DC h8: 6,6mm

Order data

Order number	114405 6,6
GTIN	4045197535115
Item class	12B

Description
Version:

Profile ground: this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

With point geometry shape C from size 2 mm

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Technical description

Number of cutting edges Z	2
Feed f in steel < 750 N/mm ²	0.07 mm/rev.
Flute length L _c	63 mm
Nominal Ø D _c	6.6 mm
Tolerance nominal Ø	h8
Shank Ø D _s	6.6 mm
Overall length L	101 mm
Standard	DIN 338
recommended maximum drilling depth L ₂	53.1 mm
Point angle	135 degrees
Shank	Plain shank
Coating	uncoated

Tool material	HSS E
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	35 m/min	P
Steel < 750 N/mm ²	suitable	28 m/min	P
Steel < 900 N/mm ²	suitable	22 m/min	P
Steel < 1100 N/mm ²	suitable	8 m/min	P
Steel < 1400 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	8 m/min	M
Oil	suitable		
wet maximum	suitable		