



Jobber drill HSS-E N, uncoated, Ø DC h8: 5,9mm



Order data

Order number	114405 5,9
GTIN	4045197535047
Item class	12B

Description

Version:

Profile ground: this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

With point geometry shape C from size 2 mm

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Technical description

Flute length L_c	57 mm
Nominal $\varnothing D_c$	5.9 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.05 mm/rev.
Number of cutting edges Z	2
Tolerance nominal \varnothing	h8
Shank $\varnothing D_s$	5.9 mm
Overall length L	93 mm
Standard	DIN 338
recommended maximum drilling depth L_2	48.2 mm
Point angle	135 degrees
Shank	Plain shank
Coating	uncoated

Tool material	HSS E
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	35 m/min	P
Steel < 750 N/mm ²	suitable	28 m/min	P
Steel < 900 N/mm ²	suitable	22 m/min	P
Steel < 1100 N/mm ²	suitable	8 m/min	P
Steel < 1400 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	8 m/min	M
Oil	suitable		
wet maximum	suitable		