



## Sheet metal slitter / shears, Type: 723034



### Order data

Order number	078102 723034
GTIN	4014586874876
Item class	03F

### Description

#### Version:

#### Aviation snips.

- Cuts well round curves with only minor sheet metal deformation.
- Comfortable and quick for seaming and cutting to length.
- For sheet metal up to 800 N/mm<sup>2</sup> and stainless steels.
- Four-way changeover blade: cleaner, burr-free cutting with low operating costs.

### Technical description

maximum material thickness steel 800 N/mm <sup>2</sup>	1 mm
Manufacturer's designation	BLS 1.6E
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum material thickness steel 400 N/mm <sup>2</sup>	1.6 mm
Cutting speed	5 - 8 m/min
Radius of the smallest curve	15 mm
Power consumption	350 W

Rate of strokes	4000 min <sup>-1</sup>
Cable length	5 m
Cutting width	0 mm
Weight	1.6 kg
Power supply	Mains-powered
Type of product	Scissors