

**Garant****GARANT Diabolo solid carbide HPC drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 5,9mm****Order data**

Order number	122642 5,9
GTIN	4045197971890
Item class	11E

**Description****Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Convex major cutting edges** with **defined honed edge** ensure the drill has high stability and maximum load capacity.

**Special multi-nano layer coating** for drilling in hardened steels.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Shank Ø $D_s$	6 mm
Feed $f$ in steel < 60 HRC	0.08 mm/rev.
Nominal Ø $D_c$	5.9 mm
Flute length $L_c$	44 mm
Number of cutting edges $Z$	2
Tolerance nominal Ø	h7
Overall length $L$	82 mm
Standard	DIN 6537
recommended maximum drilling depth $L_2$	35.2 mm
Series	Diabolo
Coating	TiAlN

## Data sheet

Tool material	Solid carbide
Version	6×D
Type	H
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	red
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	90 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	55 m/min	P
Steel < 55 HRC	suitable	28 m/min	H
Steel < 60 HRC	suitable	16 m/min	H
Steel < 65 HRC	suitable	14 m/min	H
Steel < 67 HRC	suitable	10 m/min	H
TOOLOX 33	suitable only under restricted conditions	30 m/min	H
TOOLOX 44	suitable only under restricted conditions	28 m/min	H
HARDOX 500 < 1600 N/mm <sup>2</sup>	suitable only under restricted conditions	28 m/min	H

## Data sheet

GG(G)	suitable	70 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable		