



Grinding disc CC-GRIND-STRONG, Disc Ø: 125mm



Order data

Order number	566366 125
GTIN	4007220104484
Item class	550

Description

Version:

CC-GRIND-STRONG innovative 4-layer grinding disc combines the classic roughing disc with an underlay incorporating three layers of abrasive grit which gradually wear away. **Service life advantage compared to the CC-GRIND-SOLID abrasive disc**, because of the aggressive middle layers of grit and backing pad that wears away.

Application:

For **hard and rough abrasive tasks** in surface grinding, weld seam dressing, deburring, chamfering and descaling.

Technical description

Disc Ø	125 mm
Bore Ø	22.23 mm
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
optimised for material	Steel
recommended approach angle	5-15 degrees

maximum circumferential speed	80 m/s
Type of product	Grinding wheel

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		