



Cordless impact wrench, Type: M12FID

Order data

| | |
|--------------|---------------|
| Order number | 074010 M12FID |
| GTIN | |
| Item class | 03L |

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**
- **Compact impact wrench (130 mm long) with 1/4 inch HEX bit holder.**
- **DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques.**

Supplied with:

Supplied with charger, 2× Li-ion batteries, HD box, belt clip (only M18FIW12). Supplied with 2× Li-ion high-power batteries, charger, HD box.

Note:

See No. 073808 ff. for suitable spare batteries and accessories.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Manufacturer's designation: M12 FID

Battery voltage: 12 V

Battery capacity: 2 A·h

maximum torque 1st step: 147 N·m

maximum screw Ø (8.8 - 12.9): M14

Number of impacts 1st stage: 0 - 4000 rpm

Technical description

Type of product

