



Cordless hammer drill / driver, Type: M12FPD2



Order data

| | |
|--------------|----------------|
| Order number | 070110 M12FPD2 |
| GTIN | 4058546029746 |
| Item class | 03L |

Description

Version:

- **Powerful cordless 2-speed hammer drill / driver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ compact cordless hammer drill/driver with only 168 mm tool length. 16-stage electronic torque adjustment plus drill step plus hammer drill mode.

Advantage:

Only 168 mm overall.

Supplied with:

Supplied with 2 pcs. Li-ion batteries, charger, transport case (HD box) and belt clip.

Note:

See from No. 073814 and 073840 for suitable batteries and chargers. Suitable Bluetooth tracking module can be found in the online shop.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V
 Manufacturer's designation: M12 FPD2
 Number of rechargeable batteries contained: 2
 Type of rechargeable battery: Lithium-ion
 Battery capacity: 2 A·h
 Battery voltage: 12 V
 Motor design: FUEL™

Technical description

| | |
|---|------------------------------|
| Weight | 1.2 kg |
| maximum twist drill size Ø in wood | 35 mm |
| maximum twist drill size Ø in steel | 13 mm |
| maximum vibration to EN without hammer drill function | <2.5 m/s ² |
| maximum vibration to EN with hammer drill function | 30.8 m/s ² |
| maximum twist drill size Ø in concrete | 13 mm |
| Manufacturer's designation | M12 FPD2 |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 12 V |
| maximum torque | 37 N·m |
| Packaging | Modular case (HD=Heavy Duty) |
| Type of rechargeable battery | Lithium-ion |
| Number of rechargeable batteries contained | 2 |
| Battery voltage | 12 V |
| maximum speed 2nd speed | 1700 min ⁻¹ |
| Battery capacity | 2 A·h |
| maximum speed 1st speed | 0 - 450 min ⁻¹ |
| typical application | Strong |
| Motor design | FUEL™ |
| Quick-clamping chuck range | 1.5 - 13 mm |
| Power supply | Rechargeable battery-powered |
| Suitable for material | Stone |
| Suitable for material | Steel |

| | |
|-----------------------|----------------------------|
| Suitable for material | wood |
| Suitable for material | Concrete |
| Suitable for material | Masonry |
| Type of product | limpact drill /screwdriver |

Accessories

| | |
|--|----------------|
| Li-ion system M4B2/M12B2 Rechargeable battery type, battery voltage MB12 V | 073814 MB12 |
| Battery charger Type M1218C | 073840 M1218C |
| Battery charger Type M1218FC | 073840 M1218FC |