



Cordless hammer drill / driver without battery or charger, Type: M12FPD2



Order data

Order number	070111 M12FPD2
GTIN	4058546029739
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill / driver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

Low-maintenance, brushless Powerstate motor. FUEL™ compact cordless hammer drill/driver with only 168 mm tool length. 16-stage electronic torque adjustment plus drill step plus hammer drill mode.

Feature:

Low-maintenance, brushless Powerstate motor.

Advantage:

Only 168 mm overall.

Supplied with:

Zero version – without battery, charger or transport case, with belt clip.

Note:

See from No. 073814 and 073840 for suitable batteries and chargers. Suitable Bluetooth tracking module can be found in the online shop.

See No. 073839 for a suitable starter set.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Manufacturer's designation: M12 FPD2

Battery capacity: 2 A·h

Battery voltage: 12 V

Motor design: FUEL™

maximum torque: 37 N·m

maximum speed 1st speed: 0 - 450 min⁻¹

Technical description

maximum vibration to EN with hammer drill function	30.8 m/s ²
maximum speed 1st speed	0 - 450 min ⁻¹
Battery voltage	12 V
maximum twist drill size Ø in concrete	13 mm
maximum torque	37 N·m
maximum speed 2nd speed	1700 min ⁻¹
maximum twist drill size Ø in steel	13 mm
Motor design	FUEL™
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Weight	1.2 kg
typical application	Strong
maximum vibration to EN without hammer drill function	< 2.5 m/s ²
Battery capacity	2 A·h
Packaging	Modular case (HD=Heavy Duty)
Quick-clamping chuck range	1.5 - 13 mm
Manufacturer's designation	M12 FPD2
maximum twist drill size Ø in wood	35 mm
Power supply	Rechargeable battery-powered
Suitable for material	Concrete

Suitable for material	wood
Suitable for material	Steel
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

Accessories

Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
Li-ion system M4B2/M12B2 Rechargeable battery type, battery voltage MB12 V	073814 MB12