



## External micrometer with disc anvils $\varnothing$ 30 mm, Measuring range: 125-150mm



### Order data

Order number	422992 125-150
GTIN	4250099616552
Item class	46P

### Description

#### Version:

Disc anvil of hardened steel in flat version, **without recess**. Hardened and ground measuring spindle. Higher accuracy than **DIN 863**. Locking by clamping device. With ratchet and hand temperature protection. Clearly engraved black divisions and numerals.

#### Application:

For determining the tooth widths of spur and helical gears from module 0.6.

### Technical description

Calibration	B1
Locking	by clamping device
Type of spindle	hardened and ground
Micrometer barrel graduations	1/100 mm
Barrel $\varnothing$	24 mm
Type of reading parts	engraved, black
Type of operating parts	Hand temperature protection
Measuring range	125 - 150 mm
Scale divisions	0.01 mm
Spindle $\varnothing$	8 mm

Error limit	6 µm
Standard	Manufacturer's standard
Ratchet	yes
Disc anvil	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

### Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 200 mm	022010 200
Calibration External micrometer without setting dimension maximum measuring range 200 mm	022000 200