



Cordless ratchet, Type: M12FIR12-0



Order data

Order number	070228 M12FIR12-0
GTIN	4058546029722
Item class	03L

Description

Version:

MILWAUKEE – cordless right angle drill and ratchet

- **REDLINK™ electronics with stepless speed control, reversible running and overload protection.**
- **LED illumination of the working area.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

Compact design for quick access for all applications, such as working on engines or gearboxes.

Brushless POWERSTATE™ motor with heavy-duty gearbox and casing for a long working life.

REDLINK PLUS™ electronics for intelligent power management.

Advantage:

REDLINK PLUS™ electronics.

Supplied with:

Without battery and without charger.

Supplied with 1/2 inch to 3/8 inch adapter.

Note:

See No. 073814 and No. 073839 for suitable batteries and chargers.

Technical description

maximum speed 1st speed	0 - 175 min ⁻¹
typical application	Strong
Weight	1.5 kg
maximum torque hard	81 Nm
Toolholder	Square 1/2 inch
Manufacturer's designation	M12FIR12-0
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Format	Impact ratchet
maximum vibration to EN	<2.5 m/s ²
Battery voltage	12 V
Number of rechargeable batteries contained	0
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Suitable for material	wood
Type of product	Screwdriver

Accessories

Battery starter set Type M12NRG4	073839 M12NRG4
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12