



VHB™ Power adhesive tape, Manufacturer's designation: 5952F



Order data

Order number	083785 5952F
GTIN	4054596308589
Item class	08M

Description

Version:

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping. For surfaces that are difficult to bond.

Application:

Suitable for metals, painted surfaces, painted wood, glass, ceramics and many plastics. For use indoors and outdoors.

Length: 11 m

Width: 19 mm

Colour: black

Short-term temperature-resistant to: 150 °C

Long-term temperature-resistant to: 90 °C

Technical description

Manufacturer's designation	5952F
Thickness	1.1 mm
Length	11 m
Colour	grey

Width	19 mm
Material of covering	Siliconised PE film
Stretch capability	300 %
Adhesive strength on steel	5.5 N/mm
Special features	damping
Special features	clings well
Storage humidity	50 - 60 %
Number of adhesive tapes	1
Type of adhesive tape	double-sided
Backing material	PE
Adhesive	Acrylate
Storage temperature	20 - 23 °C
"Best before" date	12 month
Application	Sealing
Application	Masking
Application	Attaching
temperature-resistant up to	120 - 150 °C