

Garant
Subland drill HSS 180°, vaporised, for screws: M5

Order data

Order number	117280 M5
GTIN	4045197036308
Item class	11C

Description
Version:

Drill and counterbore each with its own chip flutes and guide chamfers. This means the profile of the stepped drill is retained even after repeated regrinding.

Application:

For screw through holes to DIN-ISO 273 and screw head counterbores shape H, J, and K. Medium version to DIN 74 sheet 2.

Technical description

Flute length L_c	87 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.07 mm/rev.
$\varnothing D_1$ 1st step 180° h9	5.5 mm
$\varnothing D_2$ 2nd step 180° h8	10 mm
Number of cutting edges Z	2
for screws	M5
Step height L_1 1st step 180°	13 mm
Shank $\varnothing D_s$	10 mm
Overall length L	133 mm
Coating	vaporised
Tool material	HSS
Standard	DIN 8376

Tolerance nominal \varnothing	h9
Point angle	118 °
Helix angle	20-30 °
Shank	Parallel shank to h8
Countersink angle	180 °
Through-coolant	no
Shank tolerance	h8
Colour ring	without
Type of product	Stepped drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	45 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
GG(G)	suitable	25 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N
Oil	suitable		
wet maximum	suitable		