

**Impact drill, Type: GSB242****Order data**

Order number	075720 GSB242
GTIN	3165140944519
Item class	03B

**Description****Version:**

**Impact drill with high-performance motor** with high torque for very heavy duty applications (drilling, working with drills, masonry hole saws and hole saws) as well as screwdriving and smoothing.

- **New safety handle with innovative fastening and softgrip for secure holding of the machine.**
- **Sturdy metal gearbox for long working life.**
- **Mechanical overload clutch Anti-rotation for high working security even for the toughest applications**
- **Single-sleeve quick-change chuck with auto-lock for quick tool-changing using only one hand.**
- **Rotatable brush plate for equal torque in clockwise and anti-clockwise directions.**
- **Spindle neck Ø 43 mm (European standard) – can be used in drill stands.**
- **2-speed gearbox.**
- **Enhanced user protection by KickBack Control.**

**Supplied with:**

Supplied with 13-mm quick-change chuck, additional handle, depth stop 210 mm, carrying case.

**Technical description**

Power consumption	1100 W
-------------------	--------

Manufacturer's designation	GSB 24-2
Drill chuck adapter	1/2 inch – 20 UNF
maximum vibration to EN	14.6 m/s <sup>2</sup>
maximum twist drill size Ø in concrete	22 mm
maximum twist drill size Ø in steel	16 mm
maximum speed 2nd speed	3000 min <sup>-1</sup>
maximum speed 1st speed	900 min <sup>-1</sup>
Quick-clamping chuck range	1.5 - 13 mm
maximum torque	40 Nm
maximum hammer rate	15300 min <sup>-1</sup>
Weight	2.9 kg
maximum twist drill size Ø in wood	40 mm
Packaging	Carrying case
Power supply	Mains operated
Type of product	Impact drill