



Angle grinder GWS, Type: 18125LINOX



Order data

Order number	077109 18125LINOX
GTIN	3165140923927
Item class	03C

Description

Version:

High performance angle grinder with **best handling through ergonomic handle** and best weight-to-power ratio for continuous use and working overhead.

- **Powerful 1800 W motor with constant-speed electronics, smooth start-up, start-up current limitation and overload protection.**
- **High protection of the user by vibration control auxiliary handle, kick-back stop and restart inhibit.**

Reduced speed, with **very high torque** and high load factor for the heaviest duties.

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Manufacturer's designation: GWS 18-125 L stainless steel

Power consumption: 1800 W

Speed range: 8100 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 34 mm

Weight: 2.5 kg

Technical description

maximum cutting depth	34 mm
Power consumption	1800 W
Weight	2.5 kg

Data sheet

Restart block	yes
maximum disc Ø	125 mm
Manufacturer's designation	GWS 18-125 L stainless steel
Special features	High torque, ergonomic handle
maximum vibration to EN	6 m/s ²
Speed range	8100 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder