



## Angle grinder Battery, Manufacturer's designation: 71200161

### Order data

Order number	077106 71200161
GTIN	4014586888361
Item class	03F

### Description

#### Version:

**Dust-resistant and powerful 18 V / 5.2 Ah cordless angle grinder** for effective cutting, grinding and deburring work in assembly applications.

- **Maintenance-free brushless EC motor with innovative cooling ribs for optimum cooling, including temperature monitoring.**
- **Maximum work progress with FEIN HighPower Li-ion batteries. High-current cells with continuous high current output and 75% higher current than Li-ion batteries.**
- **Extremely smooth cutting action and anti-vibration working thanks to the independently mounted motor, decoupled from the housing, and 4 additional vibration dampers.**
- **Comprehensive user protection: Smooth start-up, restart inhibit, electronic overload protection, brake.**
- **Dust-protected, separate motor electronics in the handle area.**
- **FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.**

#### Advantage:

- **Maximum service life thanks to the next generation of brushless FEIN PowerDrive motors.**
- **Protection of the motor against aggressive ceramic and mineral dusts with a completely closed motor housing.**
- **Ideal for every application. Optimum speeds, tailored to a large number of abrasives and materials thanks to stepless, electronic speed preselection.**

#### Supplied with:

Supplied with 2 × 18 V / 5.2 Ah Li-ion battery, quick charger, protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, carrying case.

#### Note:

See no. 073832 ff. for suitable batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: CCG 18-115 BL

Battery voltage: 18 V

Battery capacity: 5.2 A·h  
Speed range: 2500 - 8500 rpm  
maximum disc Ø: 115 mm  
Weight: 2.7 kg

---

## Technical description

Packaging

Carrying case

Type of product