

**Bench grinding wheel D×T×H (mm), 200×25×51, Type: SC46****Order data**

| | |
|--------------|---------------|
| Order number | 596400 SC46 |
| GTIN | 9003172027784 |
| Item class | 53Y |

Description**Version:**

High-quality long-lasting bench grinder wheels in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

Application:

For aluminium and non-ferrous metals.

Specification:

Silicon carbide, green, hardness grade H.

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

| | |
|------------------|--------|
| Grit designation | medium |
| Grit | 46 |

| | |
|-------------------------------|---|
| Grinding medium code | SiC |
| maximum circumferential speed | 40 m/s |
| Grinding media | Silicon carbide (SiC) |
| Specification | Silicon carbide, green, hardness grade H |
| Grinding process | Bench grinder |
| Reducing ring inner Ø | 32 mm |
| Shape | 1 |
| Disc Ø D | 200 mm |
| Disc thickness T | 25 mm |
| Product name attribute | 200×25×51 |
| Bore Ø H | 51 mm |
| Type of product | Grinding wheel for off-hand grinders |