



## Hydraulic ram, Type: 1



### Order data

Order number	881800 1
GTIN	4021176005053
Item class	83U

### Description

#### Version:

Steel body with hydraulic mechanism and automatic return. Easy handling: the ram is used between extractor spindle and shaft. Clamp ram with extractor spindle and tighten ram spindle (hydraulics come into effect). If the travel is insufficient, release the ram spindle and repeat the procedure.

#### Application:

For increasing the power of mechanical extractors from Size 3. Even tightly seized parts can easily be freed.

### Technical description

Construction height	62 mm
maximum permissible extraction force	100 kN
maximum permissible torque	35 Nm
Ram cylinder Ø	14 mm
Body Ø	37 mm
Stroke	10 mm
Type of product	Hydraulic ram

