



## Hydraulic ram, Type: 2



### Order data

Order number	881800 2
GTIN	4021176005138
Item class	83U

### Description

#### Version:

Steel body with hydraulic mechanism and automatic return. Easy handling: the ram is used between extractor spindle and shaft. Clamp ram with extractor spindle and tighten ram spindle (hydraulics come into effect). If the travel is insufficient, release the ram spindle and repeat the procedure.

#### Application:

For increasing the power of mechanical extractors from Size 3. Even tightly seized parts can easily be freed.

### Technical description

maximum permissible extraction force	150 kN
Construction height	90 mm
Stroke	15 mm
maximum permissible torque	50 Nm
Ram cylinder Ø	23 mm
Body Ø	50 mm
Type of product	Hydraulic ram

