



## Three-leg extractor with pre-adjustable clamping range, Type: 3



### Order data

Order number	880950 3
GTIN	4021176006876
Item class	83U

### Description

#### Version:

Powerful extractor with high clamping force and excellent clamping. Using the adjustment wrench, the symmetrical clamping legs are easily set to the necessary spread. The part to be extracted is **positively gripped**, the **gripper jaws** cannot **jump or slip**.

For external extraction only.

#### Application:

For extracting tightly seized ball bearings, gear wheels, pulleys and similar parts.

### Technical description

Depth of reach up to	165 mm
External clamping range	50 - 200 mm
Power	10 t
Number of hooks	3
maximum torque	250 Nm
External hexagon drive	24 mm

Weight	3.5 kg
Type of product	Three-leg extractor