



Pin extractor set



Order data

Order number	882000
GTIN	4021176924569
Item class	83U

Description

Version:

Sturdy extractor (galvanised) with ergonomically shaped sliding hammer.

Application:

For extracting and pulling off parts with internal threads (taper pins or dowel pins) and ball bearings. The appropriate adapter or internal extractor is attached to the part to be extracted, which is then pulled off by firm strikes with the sliding hammer.

Supplied with:

Pin extractor in a plastic case (275×230×80 mm) with 6 threaded inserts (M3 – M10), 3 adapters for internal extractors No. 882600. For M12 the slide bar is used without a threaded insert.

Accepts threaded inserts to DIN 913.

Adapter for internal extractor: M7×M12, M10×M12, 15-16G×M12

Hammer mass: 0.9 kg

Hammer travel: 230 mm

suitable for threads: M3; M4; M5; M6; M8; M10; M12

Technical description

Hammer mass	0.9 kg
-------------	--------

Adapter for internal extractor	M7×M12, M10×M12, 15-16G×M12
Hammer travel	230 mm
suitable for threads	M3; M4; M5; M6; M8; M10; M12
Type of product	Pin extractor

Accessories

Threaded insert Type M5	882001 M5
Threaded insert Type M4	882001 M4
Adapter holder Type M7XM12	882002 M7XM12
Threaded insert Type M8	882001 M8
Threaded insert Type M3	882001 M3
Threaded insert Type M10	882001 M10
Adapter holder Type 15-16GXM12	882002 15-16GXM12
Adapter holder Type M10XM12	882002 M10XM12
Threaded insert Type M6	882001 M6