



## Two-leg extractor with quick adjustment, slender extractor legs, Type: 10



### Order data

Order number	880450 10
GTIN	4021176756306
Item class	83U

### Description

**Version:**

With **extremely slender extractor legs**.

**Application:**

Very suitable for working in tight spaces and places where access is difficult.

### Technical description

Internal capacity	70 - 180 mm
Power	2.5 t
Depth of reach up to	100 mm
External clamping range	30 - 120 mm
External hexagon drive	17 mm
maximum torque	35 Nm
Number of hooks	2
Weight	1.42 kg

Type of product

Two-leg extractor