

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 1012/07mm

Order data

Order number	260342 1012/07
GTIN	4045197979087
Item class	21T

Technical description

ISO code toolholder	A1012K SDUCR/L07
Neck width L_4	9 mm
suitable indexable insert	DC.. 0702..
Head length L_1	27.5 mm
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Setting angle κ	93 degrees
Pack of insert screws	269028 7
Clamping height L_2	11 mm
Centre offset L_3	9 mm
Insert size	7 mm
Usable depth T	5.9 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500