



EVOCam II video inspection system, Type: ECO2502



Order data

Order number	491895 ECO2502
GTIN	2050001956828
Item class	49B

Description

Version:

Digital full-HD microscope with brilliant live video image quality for precise magnification of objects. Various optional wide-field and precision lenses allow up to 300x magnification with constant image sharpness.

- **Brilliant full-HD video images (1080p / 60 fps).**
- **Large 30 : 1 optical zoom range with many magnification options (up to 300x) and 12x digital zoom.**
- **Effortless image storage either on external media (USB stick) or optional software solution (Vifox). Integrated USB3 interface.**
- **High-quality optics with modern digital technology.**
- **Fast, professional imaging for reliable results.**
- **Integrated 8-point LED ring lamp.**
- **High-quality stand versions for precision and stability.**
- **24 inch full-HD monitor with HDMI input.**

Multi-axis column stands (without base plate), focus module.

Application:

Video inspection system for goods receiving, production and development. Large detailed live image for continuous use and viewing by several users at the same time.

Supplied with:

With full HD colour monitor 24 inch, USB stick.

Lens 0.62x.

Optional extras:

EVO Cam II control panel No. 491898, LED transillumination, WiFi transmitter dongle and additional lenses (0.45 × / 1.00 ×). Lens (4 dioptre / 5 dioptre).
Base plate No. 491889.

Technical description

Stand	Column stand
Resolution individual image maximum	1920×1080 px
Lens Ø	55 mm
Resolution live image maximum	1920×1080 px
Weight	35 kg
Working distance	106 mm
Magnification (x-times)	3.1 - 93
Power supply	Mains operated
Type of product	Video inspection system

Accessories

Base plate for column stand	491889
EVOcam II control panel Type ECX155	491898 ECX155