



NC8 NC high pressure vice, Type: 125MX



Order data

Order number	360405 125MX
GTIN	2050002046979
Item class	34A

Description

Version:

Compact size: Optimum ratio between clamping range and overall length. The clamping force can be pre-set **without using tools: in 11 steps:** Jaw width 90 mm, **in 4 steps:** Jaw width 125 / 160 / 200 mm. Particularly rigid base body of GJS-60, **top and bottom faces ground; pairing accuracy 0.02 mm.**

Feature:

Fully enclosed low-maintenance nitrided spindle!

- **Increased service reliability.**
- **Optimised swarf protection.**
- **Minimised cleaning requirement.**

With 25H6 M10 holes at 200 mm pitch for zero-point clamping system.

Application:

Can be used horizontally or laterally, **since the side faces are ground to an accuracy of -0.05 mm.**

Supplied with:

2 stepped jaws (= standard!), 1 crank handle, 4 table clamps.

Optional extras:

- **Clamping stud No. 360025 - 25 M10.**
- **Adapter plates for quick jaw change Xtric No. 361293;361294 size 125.**
- **Adapter plates No. 361297; 361298 size 125.**
- **Front jaws No. 361140 – 361151.**

Note:

- **Dimensions/jaws interface NC 8 identical to the Allmatic TC / LC.**
- **NC 8 (No. 360405) supersedes the products LC (No. 360500) and TC (No. 360400).**

- Sizes 125 MX and 125 LX are supplied with jaws No. 361295 125 and No. 361296 125.

Technical description

Jaw height h	39.5 mm
Type	125
Clamping range d	131 - 313 mm
r ±0.015	118 mm
Clamping force up to maximum	40 kN
Colour code for suitable accessories	NC8
Longitudinal slot l H7	20 mm
Clamping range b	0 - 182 mm
Base body length a	398 mm
Version	Zero-point clamping system
Overall length L	483 mm
Base body height c -0.02	100 mm
m	180 mm
Cross-slot n H7	20 mm
t	144 mm
Weight	35 kg
Tenon width B ₁ -0.05	126 mm
Number of threads for workpiece back-stop	4
Series	NC8
Type of product	Machine vice

Accessories

Thread wiper set Type 125	360822 125
Stepped jaw, fixed for jaw width 125 mm	361296 125
Stepped jaw, mobile for jaw width 125 mm	361295 125

