

GEDORE
Electronic torque wrench / rotational angle wrench, with integral display E-Torc Q, maximum torque: 100N·m

Order data

Order number	655002 100
GTIN	4002805935484
Item class	60N

Description
Version:

The E-Torc Q / QR is a powerful electronic torque / rotational angle measuring wrench with the latest sensor technology and a 4.3 inch TFT display. Operation is optionally by **touch function or hardware buttons**. Curve depiction and evaluation can be displayed directly on the measuring tool. Parameter sets can be displayed with image data.

Data is exchanged between the torque wrench and stationary PC control software by means of Wi-Fi (2.4 and 5 GHz) or USB mini-port (from Windows® 7).

The signal transmission is shown visually by progress bars, acoustically by beep tone and by touch by means of vibration. Load cycle counter and date of the last calibration can be viewed via a menu.

Units of measure: Nm, lbfft.

Battery with quick-change system.

Function:

- **Torque control**
- **Torque / rotational angle control**
- **Elastic limit monitoring: Determination of the elastic limit of bolted connections on the basis of the difference quotients.**
- **Prevailing torque: All processes to VDI / VDE 2645 sheet 3.**
- **Slackening / tightening: Determination of the torque value of a bolted connection e.g. after application of the operating load.**

Application:

As an analysis and quality key. In research and development, the E-Torc Q / QR saves on costly experimental test rigs. Bolt fastening trials of tightening specifications can be performed directly on the component and documented.

Cutting dataa:
Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Supplied with:

Supplied with plug-in reversible ratchet, charger cable, data cable, 4 GB memory, USB stick with documentation, operating manual and evaluation / operation software.

In a rectangular box with foam inlay.

Note:

Please comply with the **specific national requirements!**

Accessories on request.

Technical description

Socket for plug-in head	9×12 mm
Exchangeable tool	Plug-in head
Square drive	1/2 in
Torque measuring accuracy	±1 %
Resolution	0.05 Nm
Weight	1800 g
maximum torque	100 Nm
Torque range	10 - 100 Nm
Series	E-torc
Lever length without plug-in head [l_1]	447 mm
Trigger principle	Vibration motor
Adjustable trigger value	adjustable
Overall length L	510 mm
Measurement process	Torque
Measurement process	Rotation angle
Measurement process	Strækgrænse
Measurement process	Overdrejningsmoment
Adjusted reference dimension on the torque wrench [l_2]	17.5 mm

Reversible reading	Nm
Reversible reading	lbf·ft
Feedback	displaying
Lever length including factory calibration reference dimension [L ₃]	464.5 mm
Display	digital
Setting the trigger value	digital, adjustable
Standard	Manufacturer's standard
Connection format	for plug-in heads (rectangular socket)
Calibration	O3
Calibration	O5
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Interface	USB interface
Measuring accuracy rotational angle	±1 %
Data can be recorded	yes
Measurement technology	electronic
Release signalling	optisk
Release signalling	akustisk
Release signalling	haptisk
Power supply	Rechargeable battery-powered
Type of product	Torque Wrench

Services

DAkkS calibrationTorque wrench clockwise / anti-clockwise maximum torque 1000/2 N·m	020040 1000/2
CalibrationRotation angle Type W	020070 W
CalibrationTorque wrench clockwise / anti-clockwise maximum torque 400/2 N·m	020030 400/2

