

Storage shelf, add-on rack, Depth 400 mm, Height / Shelf width: 2500/750mm**Order data**

| | |
|--------------|-----------------|
| Order number | 990502 2500/750 |
| GTIN | 4004514204974 |
| Item class | 96P |

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|-----------------|
| Rack installation | Extension rack |
| Number of profile frames | 1 |
| Assembled size add-on rack width | 756 mm |
| Number of shelves | 6 |
| Rack height | 2500 mm |
| Height | 2500 mm |
| Depth | 436 mm |
| Width | 756 mm |
| Storage shelf depth | 400 mm |
| Rack depth | 400 mm |
| Shelf width | 750 mm |
| maximum bay load | 1800 kg |
| Shelf load capacity / maximum distributed shelf load (on metal) | 150 kg |
| Shelf thickness | 25 mm |
| Height adjustment interval | 25 mm |
| Type of installation | Plug-in racking |
| Material | galvanized |
| Product name attribute | Depth 400 mm |
| Type of product | Storage shelf |

Accessories

| | |
|--|-----------------|
| Cross brace set suitable for racking width 750/1000 mm | 990855 750/1000 |
|--|-----------------|