

Garant**Jobber drill HSS-E, uncoated, Ø DC h8: 1,7 mm****Order data**

Order number	114400 1,7
GTIN	4045197017321
Item class	11B

Description**Version:**

Profile ground: this ensures high concentricity and pitch accuracy. Precision ground point. Drill for production use.

Reinforced core, bright finish.

With point geometry shape C from size 2 mm

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

Through-coolant: no

Standard: DIN 338

Tolerance nominal Ø: h8

Point angle: 130 °

Shank: Plain shank

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 17.5 mm

Flute length L_c : 20 mm

Overall length L: 43 mm

Shank Ø D_s : 1.7 mm

Feed f in steel < 900 N/mm²: 0.03 mm/rev.

Technical description

Flute length L_c	20 mm
Nominal Ø D_c	1.7 mm
Number of cutting edges Z	2
Feed f in steel < 900 N/mm ²	0.03 mm/rev.

Data sheet

Tolerance nominal \varnothing	h8
Shank $\varnothing D_s$	1.7 mm
Overall length L	43 mm
Standard	DIN 338
recommended maximum drilling depth L_2	17.5 mm
Point angle	130°
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	N
Through-coolant	no
Colour ring	red
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
TOOLOX 33	suitable	8 m/min	H
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	8 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	5 m/min	S
GG(G)	suitable	25 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N

Data sheet

Uni	suitable
Oil	suitable
wet maximum	suitable