

Garant
**Arbor for screw-in milling cutters with thread, SK 50, Thread M×length L1:
M12X281**

Order data

Order number	301314 M12X281
GTIN	4045197981400
Item class	31A

Description
Version:

Vibration damped version, arbor with vibration-damping core.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Vibration: damped

Overhang dimension A: 300 mm

Bore $\varnothing D_1$: 12.5 mm

$\varnothing D_2$: 21 mm

External $\varnothing D$: 49 mm

Reach L_1 : 281 mm

L_2 : 7.5 mm

Technical description

Thread M	M12×281
L_2	7.5 mm
$\varnothing D_2$	21 mm
Overhang dimension A	300 mm
Bore $\varnothing D_1$	12.5 mm
Reach L_1	281 mm

External Ø D	49 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor