



Torque screwdriver with digital display, to take D 6.3 bits, maximum torque: 50cNm



Order data

| | |
|--------------|---------------|
| Order number | 659913 50 |
| GTIN | 7610733288939 |
| Item class | 63D |

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

Torque adjustment **without using tools** just pull the cap and turn it. The torque setting is displayed in a window (**digital display at the end of the handle**). Built-in electronics with NFC interface. Battery can be replaced by the customer (button cell CR 1/3 N; 3V). **Units of measure:** Nm, lbfft.

Bit holder with magnet to take C 6.3 bits.

Application:

For controlled tightening of screws to a pre-set torque.

Standard:

Tested to DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

| | |
|----------------|--------------|
| maximum torque | 50 cNm |
| Resolution | 1 cNm |
| Bit socket | D 6,3 |
| Torque range | 0.1 - 0.5 Nm |

| | |
|----------------------------|---------------------------------|
| Torque measuring accuracy | ±6 % |
| Torque range | 10 - 50 cNm |
| Display | digital |
| Feedback | triggering |
| Measurement process | Torque |
| Trigger principle | mechanical short-travel release |
| Adjustable trigger value | adjustable |
| Standard | DIN EN ISO 6789 |
| Weight | 72 g |
| Setting the trigger value | digital, adjustable |
| Connection format | Bit holder 1/4 inch |
| Overall length L | 127.5 mm |
| Reversible reading | Nm |
| Reversible reading | lbfft |
| Calibration | O1 |
| Direction of tightening | Right-hand tightening |
| Test certificate | Manufacturer's test certificate |
| Data can be recorded | no |
| Measurement technology | mechanical |
| Release signalling | acoustic |
| Manufacturer's designation | DigiTorque V2 |
| Torque fixed setting | no |
| Type of product | Torque screwdriver |

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/659913-50>