



Torque screwdrivers with digital display, to take D 6.3 bits, maximum torque: 200cNm



Order data

Order number	659913 200
GTIN	7610733276325
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

Torque adjustment **without using tools** just pull the cap and turn it. The torque setting is displayed in a window (**digital display at the end of the handle**). Built-in electronics with NFC interface. Battery can be replaced by the customer (button cell CR 1/3 N; 3V). **Units of measure:** Nm, lbfft.

Bit holder with magnet to take C 6.3 bits.

Application:

For controlled tightening of screws to a pre-set torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Bit socket	D 6,3
Torque measuring accuracy	±6 %
Display	digital
Torque range	0.4 - 2 Nm

Resolution	2 cNm
maximum torque	200 cNm
Torque range	40 - 200 cNm
Feedback	triggering
Adjustable trigger value	adjustable
Reversible reading	Nm
Reversible reading	lbfft
Trigger principle	mechanical short-travel release
Connection format	Bit holder 1/4 inch
Weight	114 g
Overall length L	146.5 mm
Standard	DIN EN ISO 6789
Setting the trigger value	digital, adjustable
Measurement process	Torque
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	acoustic
Measurement technology	mechanical
Manufacturer's designation	DigiTorque V2
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20