

**TMSERROR, Disc Ø: 125mm****Order data**

Order number	GG5675 125
GTIN	4045197575159
Item class	GGN

Description**Version:**

Coarse cleaning disc on a glass fibre pad for direct mounting on angle grinders. Hard fleece type with open structure for general-purpose use (**same as 566750**).

same as 566750.

Application:

With **glass fibre backing pad for direct clamping** on angle grinders.

For rust removal, paint removal, dressing weld seams and removing surface dirt.

Content:

20 discs / drum.

Note:

For deburring wheels for double-ended bench grinding machines, see No. 556270 onwards.

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

recommended speed	5000 - 7000 min ⁻¹
Bore Ø	22.23 mm

Disc Ø	125 mm
Grit designation	very coarse
maximum speed	10000 min ⁻¹
Degree of hardness	hard
Contents	20
Grinding medium code	SiC
Iron, sulphur and chlorine constituents	< 0.1 %
Shape description	flat
maximum circumferential speed	60 m/s
Type of product	Rough cleaning non-woven abrasive mesh

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		

wet maximum	suitable only under restricted conditions
dry	suitable

Accessories

Coarse cleaning disc (SiC) Disc Ø 125 mm	566750 125
--	------------