



Safety cabinet Q-Classic type 30, Width: 600mm



Order data

Order number	981035 600
GTIN	4054923086395
Item class	96G

Description

Version:

Cabinet body made of melamine resin-coated, fire-resistant special boards, door front of sheet steel.

- **Mountings for shelves at 32 mm intervals.**
- **Floor-level containment tray (satisfies StawaR).**
- **With exhaust air connection (NB 75).**
- **Lockable with profile half-cylinder, can be integrated into the company's locking system. Not compatible with the Hoffmann locking system.**

Base suitable for fork lift truck. 1-door

Application:

Storage of very small quantities of hazardous substances in working areas.

Standard:

DIN EN 14470-1, Typgeprüft (Brandkammergetestet), **30 Minuten feuerbeständig (nach Brandschutzstufe der TRGS 510 Anlage 3).**

Supplied with:

Cabinet with 3 storage shelves, perforated panel insert, and floor-level drip tray, plastic-coated, plus service log book.

Colour:

Cabinet casing anthracite grey RAL 7016, doors **signal blue RAL 5005.**

Note:

At regular intervals (annually), safety cabinets should be maintained and their operating characteristics checked by an authorised competent person.

Technical description

Volume of floor-level drip tray	22 l
Load capacity of shelf	75 kg
Depth	620 mm
Height	1947 mm
Usable depth	519 mm
Weight	164 kg
Number of perforated plate inserts	1
Number of floor-level containment trays	1
Width	564 mm
Number of shelves	3
Usable width	450 mm
Usable height	1626 mm
Height adjustment interval	32 mm
Colour selection	Body RAL 7016, fronts RAL 7035, 1004, 3020, 5010, 5005, 6011, 9010, 9006
Fire resistance	30 min
Type of product	Safety cabinet