

**HOLEX****HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7:  
14,5mm****Order data**

Order number	GG1668 14,5
GTIN	4045197986573
Item class	GGN

**Description****Version:**

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

With relieved cone.

**Same as No. 122501.**

Form HB available at the same price, using No. GG1669.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Shank Ø $D_s$	16 mm
recommended maximum drilling depth $L_2$	43.3 mm
Flute length $L_c$	65 mm
Tolerance nominal Ø	h7
Standard	DIN 6537 K

Overall length L	115 mm
Feed f in steel < 900 N/mm <sup>2</sup>	0.26 mm/rev.
Nominal Ø D <sub>c</sub>	14.5 mm
Number of cutting edges Z	2
Contents	5
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Machining strategy	HPC
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable		

---

## Accessories

HOLEX Pro Steel solid carbide drill, plain shankDIN 6535 HA  
Ø DC h7 (mm or inch) 14,5

---

122501 14,5